



High Pressure Foam Analyzer – HPFA

Specifications



Product group specifications

HPFA

Height camera

Connection	USB 2.0
Performance	5 fps at 1280 × 1024 px
Spatial resolution	200 dpi 0.12 mm/px
Mean field of view	85 × 5.2 mm ²
Focus	manual

Structure camera

Connection	USB 2.0
Performance	2 fps at 1280 × 1024 px
Mean field of view	25 × 13 mm ²
Diameter of minimum detectable bubble	150 µm
Focus	manual

Illumination for height detection

Type	LED (blue)
Wave length, dominant	469 nm

Illumination for structure detection

Type	LED (red)
Wave length, dominant	633 nm

Software

ADVANCE	foam analysis – high pressure
---------	-------------------------------

Measurement specifications

HPFA

Analyzed foam characteristic

foamability and foam stability

foam structure: homogeneity, stability and aging

Results

- foam height
- liquid height
- total height
- foam capacity¹⁾
- maximum foam density
- expansion rate
- foam half life time
- drainage half life time
- sample temperature
- gas temperature
- pressure
- mean bubble area
- bubble count per mm²
- standard deviation of mean bubble area
- bubble size distribution
- bubble count half life
- Sauter mean radius
- final foam structure

¹⁾ additional flow sensor needed

General specifications**HPFA****Pressure measurement**

Maximum pressure ²⁾ 350 bar (5000 psi)

Temperature control

Type electrical
Range from room temperature up to 120 °C

Temperature sensor

Sensor 1 thermocouple
Location in the high-pressure cell (top/middle/bottom)

Mini dosing system

Dosing manual
Location in the high-pressure cell (top/middle/bottom)
Temperature maximum 180 °C

Environment

Operating temperature 10 to 40 °C
Humidity without condensation

Instrument dimensions

Footprint 1100 mm × 640 mm (W × D)
Height 1070 mm
Weight (without accessories) ca. 190 kg

Power supply for HPFA

Voltage 100 to 240 VAC
Power consumption maximum 30 W
Frequency 50 to 60 Hz

Power supply for heating

Voltage 115/230 VAC
Power consumption maximum 1880 W
Frequency 50 to 60 Hz

Interfaces

PC 1 × USB 3.0

Accessories

Filter plates for sparging Diameter: 30 mm
Filter plate porosities G2: nominal maximum pore size: 40 to 100 µm (recommended)
G3: nominal maximum pore size: 16 to 40 µm
G4: nominal maximum pore size: 10 to 16 µm
Material of columns and frits borosilicate glass (norm: ISO 4793)
Material of sealings PTFE with glass fibers (inner) and graphite (outer) for the windows
HNBR for the filter plates

²⁾ additional external syringe pump needed

